

DUROFTAL® VPI 2803/78BAC

TYPE

Hydroxy functional polyester; cross-linkable with polyisocyanates for the production of ultra high solids lacquers

Average hydroxyl content (solid resin)

approx. 6.0 %

FORM OF DELIVERY (f.o.d.)

78 % in butyl acetate (78BAC)

PRODUCT DATA

Determined per batch:

Dynamic Viscosity DIN EN ISO 3219
dynamic viscosity [mPa.s] 7000 - 19000
(25 1/s; 23 °C)

Colour Scale (Hazen) DIN EN ISO 6271-1
Hazen colour value <= 50

Hydroxyl Value DIN EN ISO 4629 (VLN 283)
hydroxyl value [mg KOH/g] 185 - 215
(solids)

Non-Volatile Matter DIN EN ISO 3251
non-volatile matter [%] 76 - 80
(1 h; 125 °C; 2 g; EAC)

Colour / Appearance VLN 250
colour colourless
appearance clear

Not continually determined:

Density (Liquids) DIN EN ISO 2811-2
density [g/cm³] 1,14
approx.
(20 °C)

Flash Point DIN EN ISO 1523
flash point [°C] 31
approx.

SPECIAL PROPERTIES AND USE

Duroftal VPI 2803 in combination with aliphatic polyisocyanates, pre-eminently with Desmodur N 3300 (Bayer), produces high quality, ultra high solids, two pack clearcoats and pigmented topcoats for the automotive refinish and industrial lacquer sectors. Based on Duroftal VPI 2803 clearcoats with a VOC (volatile organic compound) of 350 g/l and pigmented topcoats with a VOC of at most 420 g/l can be achieved.

Cured films provide:

- high hardness
- high gloss and depth of image
- excellent solvent and chemical resistance
- superior weathering stability

DILUTABILITY

Duroftal VPI 2803 is completely dilutable with esters, ketons and toluene. With xylene and higher boiling aromatic solvents dilutability is given in a wide range. Dilutability should be tested before use.

COMPATIBILITY

In general, Duroftal VPI 2803 shows compatibility with a wide range of acrylic and polyester binders as well as with standard polyisocyanates used in two pack polyurethane lacquers. However, compatibility should be tested before use.

STORAGE

At temperatures up to 25 °C storage stability packed in original containers amounts to at least 730 days.

DISTINGUISHING FEATURES

Compared to Duroftal VPI 2801, Duroftal VPI 2803 needs a lower amount of polyisocyanate for stoichiometric crosslinking.

4.0/17.07.2013 (replaces all previous versions)

• Worldwide Contact Info: www.allnex.com •

Disclaimer: Allnex Group companies ("Allnex") decline any liability with respect to the use made by anyone of the information contained herein. The information contained herein represents Allnex's best knowledge thereon without constituting any express or implied guarantee or warranty of any kind (including, but not limited to, regarding the accuracy, the completeness or relevance of the data set out herein). Nothing contained herein shall be construed as conferring any license or right under any patent or other intellectual property rights of Allnex or of any third party. The information relating to the products is given for information purposes only. No guarantee or warranty is provided that the product and/or information is adapted for any specific use, performance or result and that product and/or information do not infringe any Allnex and/or third party intellectual property rights. The user should perform its own tests to determine the suitability for a particular purpose. The final choice of use of a product and/or information as well as the investigation of any possible violation of intellectual property rights of Allnex and/or third parties remains the sole responsibility of the user.

© 2013 Allnex Belgium SA. All Rights Reserved

Notice: Trademarks indicated with the ®, ™ or * are registered, unregistered or pending trademarks of Allnex Belgium SA or its directly or indirectly affiliated Allnex Group companies.